

Automated Inspection & Intelligent Material Handling for Buns



www.montrose-tech.com

Montrose inspection and handling systems provide a complete inspection, rejection, and handling solution created just for bun/roll manufacturing lines. Receive comprehensive statistical analysis of variability while removing human involvement from inspection, rejection, and laning.

A high speed, turnkey system that allows you to:

1. Assure quality on a 100% monitoring basis.
2. Remove individual defective and non-conforming product from the line.
3. Monitor process statistics to pinpoint causes of waste.
4. Equally feed in-spec buns into each of the packaging lanes.
5. Automatically buffer in the case of bottlenecks.
6. Rapidly recognize a positive ROI by improving quality, reducing waste, and automating production - in previously labor-intensive areas



MT-24 In-line Inspection Systems for Buns

Solution Components	SnapQC	FocalPoint	MT Series	AutoLaner
3D & True Color Inspection	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	
Bottom Color Inspection	<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	
Automated Rejection			<input checked="" type="checkbox"/>	
Laning and Entrance to Packaging				<input checked="" type="checkbox"/>
In-line Accumulation/ Buffering			<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Weight	<input checked="" type="checkbox"/>			
Statistical Analysis and Reporting	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	
NEMA 4X		<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>

Isolate and Eliminate Sources of Waste

Automated inspection provides real-time and historical information on fault, and out-of-spec conditions, allowing you to isolate the issues causing the most waste by shift, product, line, and plant. The measurement results will also make it easier to reach consistent quality when developing new products or when formulation changes are made.

Analysis Type	Example Faults	Impact on Customer or Plant	Rejection Capability	Statistical Analysis
Geometrical Analysis	Too large or small Too tall or short	Product rejection	0-100% fully under plant control	Worst Fault Pareto
	Ovality Doubles	Customer complaints		Reporting
	Poor symmetry/crushed dented	Handling problems (jamming at the slicer/bagger)		Dashboard
Color Analysis (Top and Bottom)	Under/over- baked Visible Debris	Consumer Complaints	0-100% fully under plant control	Worst Fault Pareto
	Blisters, blotchy, foreign material	Product rejection		Reporting
	Too much topping, too little topping, heel flour, white rings	Topping giveaway		Dashboard

Measure, Analyze, Reject

The **MT Series inspection system** may be installed immediately after the depanner for fast real-time data, or just before packaging where the system acts as the 'gate-keeper.' A vision system and AutoLaner combination assures smooth flow of quality buns into the slicer, with the removal of oversized product, belt speed changes, diversion, and/or lane balancing.

Automated Inspection & Intelligent Material Handling for Buns

MONTROSE
TECHNOLOGIES INC.


www.montrose-tech.com

Height Analysis



Profile height calculations are based on hundreds of individual height values gathered on every product, which leads to a measurement accuracy of $\pm 0.5\text{mm}$. **Mean Height** is another common measurement applied to buns.

2D Analysis



Two dimensional calculations are based on an accurately defined perimeter, which is imaged by both overhead cameras. 2-D measurement accuracy is $\pm 0.5\text{mm}$. **Mean Diameter, Roundness, Surface Area,** and **Volume** are other common measurements applied to buns.

Color Analysis



True color calculations, on both the top and bottom surface of the product, are measured in various units such as $L^*a^*b^*$ and BCU.

Automated Inspection & Intelligent Material Handling for Buns

MONTROSE
TECHNOLOGIES INC.

www.montrose-tech.com

Common Fault Analysis



Seed Voids
(Regional low color deviation)



Misshaped Slope
{Poor height symmetry}



Blotchy
(Regional high color deviation)



White Ring
(Light area near heel perimeter)



Blisters
(Dark Surface Area)



Heel Flour
(Very light heel area)



Double/Triple
(Large Surface Area)

Only common examples have been pictured. There are many standard measurements that can be used, individually or combined within formulae, to qualify your product. **All visible product characteristics and faults can be quantified.**